

ELIGHT(IPL+BIPOLAR RF)



Specifications	E-Light
Lamp-house	Super intense pulsed light
Range of Spectrum	480-1200nm: remove acne
	530 -1200nm: speckle treatment
	560 -1200nm: skin rejuvenator
	590-1200nm: remove vessel
	640 -1200nm: remove unwanted hair
RF Frequency	6MHZ
RF Maximum Out	Maximum:100J/CM3
Density of Energy	1~50J/cm2
Size of Spot	8*40mm2, 16*50 mm2
Amount of pulse	1~6,adjustable
Interval of Pulse	1~99ms,adjustable
Sub-pulse Width	0.1~9.9ms,adjustable
Cycle	1~4s,adjustable
Pulse Rate	0.3Hz, 0.5Hz, 1Hz,2Hz, adjustable
Cooling Way	semi-conductor cooling
Screen	5.7 /8.4 inch color touch screen
Power Supply	220V ±10% 50Hz ;110V ±10% 60Hz
Weight	30-50kg
Price Please ask!	Click here!

- Remove speckles and other pigment problems
- Skin rejuvenation, pore minimizing
- Treat blood vessel and telangiectasis
- Treat acne mark and other scars
- Remove unwanted hair
- Wrinkle removal

FEATURES

- + PL and Bipolar RF two systems in one machine and it can work separately
- + Permanent hair removal for various hair color
- + 24 hours continuous work
- + 5.7/8.4 inch color touch LCD display, multi-